



ACCESSIBLE BATHROOMS

### Ella Gel Coat Walk In Baths Comparison Chart

Options: S - Soaking, A - Air Massage, H - Hydro Massage, D - Dual Massage (hydro & air)

| Important Dimensions (Inches)         | Narrow 26" Wide | Short 48" Long | Small 45" Long | Front Entry | Deep 46" High | Bariatric 30.5" Seat | Low 3.5" Threshold | Lay Down    | Long     |
|---------------------------------------|-----------------|----------------|----------------|-------------|---------------|----------------------|--------------------|-------------|----------|
| Dimensions of Tub WxLxH               | 26x53x40        | 28x48x40       | 26x45x40       | 33x38x38    | 30x55x46      | 35x55x41             | 30x51.5x41         | 30x60x22.25 | 32x60x68 |
| Dimensions of Crate WxLxH             | 27x54x42        | 29x49x43       | 27x46x43       | 34x39x39    | 31x56x48      | 36x56x44             | 31x52x42           | 31x61x24    | 33x61x40 |
| Extension Panel to fit in 60" opening | 7"              | 12"            | 15"            | N/A         | 5"            | 5"                   | 8"                 | N/A         | N/A      |
| Threshold Height                      | 6.83"           | 6.83"          | 6.25"          | 6.85"       | 6.83"         | 5"                   | 3.5"               | 5"          | 6"       |
| Threshold Option                      | N/A             | N/A            | N/A            | N/A         | N/A           | N/A                  | N/A                | N/A         | N/A      |
| Seat width                            | 19.5"           | 22"            | 16"            | 21.5"       | 22"           | 30.5"                | 20.5"              | N/A         | 21.5"    |
| Seat Height                           | 17"             | 17"            | 17"            | 17"         | 17"           | 17"                  | 17"                | N/A         | 17"      |
| Width of Door                         | 16"             | 15"            | 15"            | 30"         | 18"           | 23.5"                | 17.5"              | 18"         | 18"      |

| Important Data                       | Narrow 26" Wide | Short 48" Long | Small 45" Long | Front Entry           | Deep 46" High | Bariatric 30.5" Seat | Low 3.5" Threshold | Lay-Down      | Long          |
|--------------------------------------|-----------------|----------------|----------------|-----------------------|---------------|----------------------|--------------------|---------------|---------------|
| Gallons USA (Unoccupied)             | 85              | 60             | 55             | 50                    | 115           | 170                  | 90                 | 50            | 115           |
| Gallons USA (Occupied)               | 40-60           | 32-45          | 28-48          | 23-38                 | 80-100        | 90-150               | 55-75              | 24-45         | 80-100        |
| Suggested Water Heater (Gallons USA) | 50              | 50             | 40             | 40                    | 80            | 80                   | 60                 | 40            | 80            |
| Drainage Time (approximate)          | 3 Min           | 3 Min          | 3 Min          | 3 Min                 | 4.5 Min       | 5 Min                | 3 Min              | 3 Min         | 3 Min         |
| Drain/Door Location                  | Right or Left   | Right or Left  | Right or Left  | Right or Left (Hinge) | Right or Left | Right or Left        | Right or Left      | Right or Left | Right or Left |
| Product Net Weight LBS               | 235             | 190            | 190            | 180                   | 245           | 310                  | 255                | 205           | 225           |
| Product Shipping Weight LBS          | 300             | 210            | 210            | 200                   | 280           | 360                  | 280                | 250           | 260           |

| Features                      | Narrow 26" Wide | Short 48" Long | Small 45" Long | Front Entry | Deep 46" High | Bariatric 30.5" Seat | Low 3.5" Threshold | Lay-Down | Long       |
|-------------------------------|-----------------|----------------|----------------|-------------|---------------|----------------------|--------------------|----------|------------|
| Grab Bar                      | 1               | 1              | 1              | N/A         | 1             | 1                    | 1                  | N/A      | 1          |
| Thermostatic Control Valve    | N/A             | N/A            | N/A            | N/A         | N/A           | N/A                  | N/A                | N/A      | N/A        |
| Water supply lines            | 3/4"            | 3/4"           | N/A            | N/A         | 3/4"          | 3/4"                 | 3/4"               | 3/4"     | 3/4"       |
| Pull Out Hand Mixer Hose      | S, A, H, D      | S, A, H, D     | S, A, H, D     | S, A, H, D  | S, A, H, D    | S, A, H, D           | S, A, H, D         | S, A, H  | S, A, H, D |
| Textured Slip Resistant Floor | S, A, H, D      | S, A, H, D     | S, A, H, D     | S, A, H, D  | S, A, H, D    | S, A, H, D           | S, A, H, D         | S, A, H  | S, A, H, D |
| Number of Access Panels       | 2               | 2              | 2              | N/A         | 2             | 1                    | 2                  | 1        | 2          |
| Hydro jets                    | 6               | 6              | 6              | 4           | 6             | 6                    | 6                  | 6        | 6          |
| Air jets                      | 18              | 18             | 18             | 14          | 18            | 18                   | 18                 | 16       | 18         |
| In-line water heater          | H, D            | H, D           | H, D           | H, D        | H, D          | H, D                 | H, D               | H        | H, D       |
| In-line air heater            | A, D            | A, D           | A, D           | A, D        | A, D          | N/A                  | A, D               | A        | A, D       |
| Ozone Sterilization           | Optional        | Optional       | Optional       | Optional    | Optional      | Optional             | Optional           | Optional | Optional   |
| LED Chromatherapy             | Optional        | Optional       | Optional       | Optional    | Optional      | Optional             | Optional           | Optional | Optional   |
| Removable Swivel Tray         | N/A             | N/A            | N/A            | N/A         | N/A           | N/A                  | N/A                | N/A      | N/A        |
| Removable Rubber Back Support | N/A             | N/A            | N/A            | N/A         | N/A           | N/A                  | N/A                | N/A      | N/A        |
| Aromatherapy                  | Optional        | Optional       | Optional       | Optional    | Optional      | Optional             | Optional           | Optional | Optional   |
| Heated Back Rest              | Optional        | Optional       | Optional       | Optional    | Optional      | Optional             | Optional           | Optional | Optional   |